

Dedicated Tungsten Grinder for Continuous Grinding of .040" to 3/32" (1.0mm-2.4mm)

The New Piranha II Features:

- Sliding dust shield for 100% dust containment
- Integrated receptacle area for ease of handling electrodes
- Recessed handle for better form & function
- On/off switch with LED light for improved display of unit operation
- Lightened chassis for reduced weight
- Signature blue powdercoat

Safetv

Enclosed grinding area captures Tungsten dust for easy disposal.

Weld Quality

20 Ra surface finish improves Tungsten life, arc starting, arc stability and produces consistent weld penetration.

Productivity

Correctly and consistently Diamond grind Tungsten Electrodes longitudinally, in less than 30 seconds.

Value

The PIRANHA II Diamond grinds, flats and notches your Tungsten economically.



"The Tungsten Electrode Experts"

Features

- Easy set up, optimal consistency and near-perfect repeatability.
- Compact, durable and solid design with no vibration.
- Longitudinal 20 RA grinding for maximum arc starting, arc stability, electrode life and weld penetration.
- Universal collet arm for 3 electrode sizes 040" (1.0mm), 1/16" (1.6mm), 3/32" (2.4mm) with no equipment changes.
- Included angle scale for angles from 10° 60°
- Precision tip flat gauge & depth adjustment stop ensures exact Tungsten points every time – enabling consistent, repeatable arc performance and welding output.
- Dust shield & Containment baffle to keep dust inside the grinder housing, for safety and easy disposal.
- Tip flat block for square end grinding and removing bad tips.
- Electrode notching station for simple cut-off.
- Double-sided grinding wheel for maximum wheel life and value.
- Detailed Manual with valuable engineering data and welding recommendations.
- Integrated receptacle for electrode storage/access
- Recessed carry handle for better form and function



Additional Products

DGP-KIT-PIIs Piranha II Collet Upgrade Kit Get the performance of the new Piranha tungsten grinders without having to buy a new grinder! Our new Piranha II collet upgrade kit cal be used on your older model Piranha tungsten grinder to enable you to grind tungsten as short as .75" (19.05mm). The process and directions are simple.



Full feature Precision Tungsten Grinders: These high precision, heavy duty grinders provide additional features for improved grinding accuracy and can precisely cut electrodes to length.

CNC Pre-Ground Electrodes: Eliminates operator grinding variables. The quality and consistency of CNC Pre-Ground Electrodes improve arc starting and arc stability. They offer consistent weld penetration and longer electrode life. Tungsten shedding and associated weld inclusions have been virtually eliminated.

- Piranha III Compact/Precision Tungsten Grinder .040" - 3/16" (1.0 - 4.8mm)
- DGP-2 Full feature Tungsten grinder that grinds, flats and cuts Tungsten.
- Pre Ground Electrodes CNC manufactured, high tolerance electrodes for Orbital and Automatic Tig and Plasma welding.
- Premium Tungsten Thoriated, Lanthanated, Ceriated, Zirconiated, Tri-Mix™-WS2, Cryo-T, Pure & specialty materials.

Specifications

Range of Included Angle: 10° - 60°

Electrode Diameters: .040 (1.0 mm), 1/16"

(1.6 mm), 3/32" (2.4 mm)

Minimum Electrode Length: 1.75" (44.5 mm)

Voltage: 110/220 VAC, 50/60 Hz

Power Consumption: 40 Watts

Motor:2,500 rpm, .5 ampsLength:7.750" (196.85mm)Width:4.750" (120.65 mm)Height:6.000" (152.4 mm)Weight:10 lbs (4.54 kg)

Benefits

- Safety: Enclosed grinding area captures Tungsten dust for easy disposal.
- Weld Quality: 20 Ra surface finish improves Tungsten life, arc starting, arc stability and produces consistent weld penetration.
- Productivity: Longitudinally Diamond grind your Tungsten electrode in less than 30 seconds correctly and consistently.
- Value: The PIRANHA II Diamond grinds, flats and notches your Tungsten economically.



US Office: 2651 Lavery Court • Newbury Park, CA 91320 Tel: 805-498-3837 • Fax: 805-498-9347

European Office: Diamond Ground Products Europe Blackstone Road, Huntingdon, Cambridgeshire, PE29 6EF, UK Tel: 01480 437478 ● Fax: 01480 437479